

INDUCTIVE PROXIMITY SWITCH

NJ6.5-E2S

Order no.	NJ6.5-E2S
General data	
Certification	CE
Basic standard	IEC 60947-5-2
Protection to IEC 60529	IP67
Function display	Yes
Protected against polarity reversal	Yes
Power indicator	No
Short-circuit-proof	Yes
Electrical data	
Connection type	Connector
Effective operating voltage [V DC]	24
Rated insulation voltage [V DC]	75
Load current capacity [mA]	200
Rated short circuit current [A]	100
Supply voltage min. [V DC]	10
Supply voltage max. [V DC]	30
Electrical version	DC, direct current
Minimum operating current [mA]	0
Load capacitance max. [μ F]	500
No-load current damped max. [mA]	9
Max. no-load current undamped [mA]	3
Ripple max. [%]	15
Switching output	PNP
Switching frequency [Hz]	3000
Switching function	Normally open (NO)
Voltage drop [V]	2.5
Mechanical data	
Mounting length [mm]	32.3
Rated operating distance S_n [mm]	1.50
Installation type	flush
Housing Material	Stainless steel
Assured switching distance S_a [mm]	1.20
Effective operating distance S_r [mm]	1.5
Sensor- \varnothing [mm]	6.5
Connector type	M8x1
Depth [mm]	46.0
Ambient temperature range [$^{\circ}$ C]	-25 ... +70
Active surface material	PBT

