HANDLING COMPONENTS

COMPACT LINEAR CYLINDERS - SERIES SHD

▶ PRODUCT SPECIFICATIONS



Note

SH cylinder can be combined with suction cups via nozzles

ZUB0028 - Fixing type 2

ZUB0029 - Fixing type 1

Special features

Integrated venturi nozzle for vacuum generation

► RECOMMENDED ACCESSORIES



Nozzle

ZUB0028



Nozzle

ZUB0029



Mounting block

КВЗМ



Inductive proximity switch - Cable 5 m

NJ3-E2




Flow Control Valves - with Swivel joint

DRVM5X4

	► Technical Data*			
Order no.	SH7	SH15	SH25	SH50
Stroke [mm]	7	15	25	50
Pressure force max. [N]	170	170	170	170
Retraction force [N]	100	100	100	100
Air volume per cycle [cm³]	4	9	15	30
Operating temperature [°C]* *	5 +80	5 +80	5 +80	5 +80
Weight [kg]	0.09	0.1	0.13	0.18

^{*}All data measured at 6 bar



 $^{^{*\,*}\}mbox{High-temperature-resistant}$ model (up to 150°C) add T to part number