


# SPN ZERO-POINT CLAMPING SYSTEM

## SPN112P2 - CLAMPING PLATE


### ► 2-FOLD



- Compact design with optimized design height
- System assembly with high precision
- Integrated air supply/distribution
- Integrated PLUS connection
- Available with the advanced zero-point clamping system on request
- Variable mounting options

#### ► Technical Data

Order no.	SPN112P2E6SD-B	SPN112P2E4SD-B
Operation mode	Pneumatic	Pneumatic
Holding force max.	2xM10/M12	2xM10/M12
Operating pressure [bar]	6 ... 7	4 ... 7
Pull-in force [kN]	6.0	4.0
Pull-in force with PLUS connection [kN]	2x15	2x10
Operating temperature [°C]	-10 ... +70	-10 ... +70
Rotation prevention	Yes	Yes
PLUS connection	Yes	Yes
Air cleaning	No	No
Piston position sensing	No	No
Contact monitoring	No	No
Material	Tempered stainless steel/steel	Tempered stainless steel/steel
Weight [kg]	19	19



- ① Release
- ② Plus connection
- ⑥ Mounting screw\*
- ⑦ Thread bore transport
- ⑧ Sealing cap
- ⑨ T-slot nut\*
- ⑩ T-slot nut mounting screw\*

\*Not included in delivery