SPN ZERO-POINT CLAMPING SYSTEM **SPN138P2 - CLAMPING PLATE**

> 2-FOLD



- Compact design with optimized design height
- System assembly with high precision
- Integrated air supply/distribution
- ► Integrated PLUS connection
- Available with the advanced zero-point clamping system on request
- Variable mounting options

	► Technical Data	
Order no.	SPN138P2E6SD-B	SPN138P2E4SD-B
Operation mode	Pneumatic	Pneumatic
Holding force max.	2xM12/M16	2xM12/M16
Operating pressure [bar]	6 7	4 7
Pull-in force [kN]	18.0	12.0
Pull-in force with PLUS connection [kN]	2x36	2x24
Operating temperature [°C]	-10 +70	-10 +70
Rotation prevention	Yes	Yes
PLUS connection	Yes	Yes
Air cleaning	No	No
Piston position sensing	No	No
Contact monitoring	No	No
Material	Tempered stainless steel/steel	Tempered stainless steel/steel
Weight [kg]	28	28

