
SPN ZERO-POINT CLAMPING SYSTEM SPN138P4 - CLAMPING PLATE

▶ 4-FOLD



- Compact design with optimized design height
- System assembly with high precision
- Integrated air supply/distribution
- ► Integrated PLUS connection
- Available with the advanced zero-point clamping system on request
- Variable mounting options

	► Technical Data	
Order no.	SPN138P4E6SD-B	SPN138P4E4SD-B
Operation mode	Pneumatic	Pneumatic
Holding force max.	4xM12/M16	4xM12/M16
Operating pressure [bar]	6 7	4 7
Pull-in force [kN]	18.0	12.0
Pull-in force with PLUS connection [kN]	4x36	4x24
Operating temperature [°C]	-10 +70	-10 +70
Rotation prevention	Yes	Yes
PLUS connection	Yes	Yes
Air cleaning	No	No
Piston position sensing	No	No
Contact monitoring	No	No
Material	Tempered stainless steel/steel	Tempered stainless steel/steel
Weight [kg]	54	54



- (1) Release
- 2 Plus connection
- 6 Mounting screw*
- 7 Thread bore transport
- (8) Sealing cap
- 9 T-slot nut*
- 10 T-slot nut mounting screw*
- *Not included in delivery