

VACUUM CARTRIDGE

SERIES ZVC | INSTALLATION SIZE ZVC252

▶ PRODUCT ADVANTAGES



▶ High Efficiency

High vacuum flow with low compressed air consumption for efficient operation.

▶ Lightweight and compact

An exceptionally compact and lightweight design for space-saving integration.

▶ Reliable Even When Air Pressure Fluctuates

Consistent vacuum generation even when compressed air pressure fluctuates or drops.

▶ Certifications: LABS / REACH / RoHS

▶ PRODUCT KEY



ZVC	X	30	3	NRV	HP2M25
Series	Version	Vacuum cartridge type	Number of stages of the vacuum cartridge	Throttle check valve	Retaining cap / silencer

▶ TECHNICAL DATA

Order no.	▶ Technical data			
	ZVC252	ZVC252-HP1M22	ZVC252-NRV	ZVC252-NRV-HP1M22
Max. vacuum level [kPa]	-94	-94	-94	-94
Volume flow [l/min]	113	113	113	113
Digital vacuum switch	No	No	No	No
Air-saving function	No	No	No	No
Weight [kg]	0.009	0.016	0.009	0.016
Vacuum cartridge type	Mini Premium	Mini Premium	Mini Premium	Mini Premium
Number of stages of the vacuum cartridge	2	2	2	2
Fixing thread		M22 external		M22 external
Air control valve	No	No	No	No
Blow-off control valve	No	No	No	No
Solenoid valve	No	No	No	No
Throttle check valve	No	No	Yes	Yes
Silencer	No	No	No	No
Vacuum filter	No	No	No	No
Mounting type		Retaining cap		Retaining cap
Operating pressure max. [bar]	7	7	7	7
Air consumption at 5.5 bar [l/min]	77	77	77	77
Air consumption at 6 bar [l/min]	84	84	84	84
Operating temperature [°C]	-20 ... +80	-20 ... +80	-20 ... +80	-20 ... +80
Certifications	LABS / REACH / RoHS	LABS / REACH / RoHS	LABS / REACH / RoHS	LABS / REACH / RoHS


▶ DIAGRAMS

ZVC252




▶ TECHNICAL DRAWINGS

ZVC252




ZVC252-HP1M22



① Fixing

ZVC252-NRV



ZVC252-NRV-HP1M22

