


VACUUM GRIPPING SYSTEM

SERIES ZGM

► PRODUCT ADVANTAGES



► Compact and flexible

The compact design of the ZGM series allows for space-saving integration and is suitable for a wide variety of applications.

► Suitable for various surfaces

Thanks to a variety of valve options, the ZGM series can be used on both dense and porous surfaces.

► High holding force with a compact design

The ZGM series offers high gripping force and is therefore particularly well-suited for applications that require high gripping forces but where only compact grippers can be used.


► Certifications: LABS / REACH / RoHS

► PRODUCT KEY


ZGM	40X150	21	FS2	A
Series	Dimensions	Levels and number of vacuum cartridges	Valve technology and hole pattern	Air and blow-off control valve, sensor

► DIAGRAMS


ZGM16 round




ZGM20 round




ZGM40 round




ZGM40 oval



ZGM50 round




ZGM50 oval




TECHNICAL DRAWINGS

ZGM16X60




- ② Pneumatic connection ⑫ Vacuum switch connection
⑤ Exhaust air/exhaust air valve

ZGM16X108




- ② Pneumatic connection ⑫ Vacuum switch connection
⑤ Exhaust air/exhaust air valve

ZGM20X60



- ② Pneumatic connection ⑫ Vacuum switch connection
⑤ Exhaust air/exhaust air valve

ZGM20X108




- ② Pneumatic connection ⑫ Vacuum switch connection
⑤ Exhaust air/exhaust air valve

VACUUM GRIPPING SYSTEM

SERIES ZGM


ZGM40



- ① Fixing
- ② Pneumatic connection


Model	L1 [mm]	L2 [mm]	L3 [mm]	L4 [mm]	L5 [mm]
ZGM40X150	83.5	33	38.5	155	15
ZGM40X200	133.5	33	38.5	205	15
ZGM40X300	233.5	33	38.5	305	15
ZGM40X400	333.5	33	38.5	405	15
ZGM40X500	433.5	33	38.5	505	15
ZGM40X600	533.5	33	38.5	605	15

ZGM40 with accessories



- ⑤ Exhaust air/exhaust air valve
- ⑨ Air control valve


ZGM50



- ① Fixing
- ② Pneumatic connection

Model	L1 [mm]	L2 [mm]	L3 [mm]	L4 [mm]	L5 [mm]
ZGM50X150	83.5	33	38.5	155	15
ZGM50X200	133.5	33	38.5	205	15
ZGM50X300	233.5	33	38.5	305	15
ZGM50X400	333.5	33	38.5	405	15
ZGM50X500	433.5	33	38.5	505	15
ZGM50X600	533.5	33	38.5	605	15

ZGM50 with accessories



- ⑤ Exhaust air/exhaust air valve
- ⑨ Air control valve

► TECHNICAL DATA

Order no.	► Technical data							
	Max. vacuum level [kPa]	Volume flow [l/min]	Air consumption at 4 bar [l/min]	Air consumption at 6 bar [l/min]	Hole pattern of the sealing element	Air control valve	Valve type of the area gripper	Weight [kg]
ZGM16X60-21	-90	41		32	Round Ø 5	No	Flow resistance	0.049
ZGM16X108-31	-90	85		32	Round Ø 5	No	Flow resistance	0.082
ZGM20X60-21	-90	41		32	Round Ø 5	No	Flow resistance	0.062
ZGM20X108-31	-90	85		32	Round Ø 5	No	Flow resistance	0.092
ZGM40X150-21-FL2	-92	171	152		Round Ø 22	No	Flow resistance	0.26
ZGM40X150-21-FL2-A	-92	171	152		Round Ø 22	Yes	Flow resistance	0.34
ZGM40X150-21-FL3	-92	171	152		Oval	No	Flow resistance	0.27
ZGM40X150-21-FL3-A	-92	171	152		Oval	Yes	Flow resistance	0.35
ZGM40X150-21-FS2	-92	171	152		Round Ø 22	No	Flow resistance	0.26
ZGM40X150-21-FS2-A	-92	171	152		Round Ø 22	Yes	Flow resistance	0.34
ZGM40X150-21-FS3	-92	171	152		Oval	No	Flow resistance	0.27
ZGM40X150-21-FS3-A	-92	171	152		Oval	Yes	Flow resistance	0.35
ZGML40X150-21-FL2	-75	200		104	Round Ø 22	No	Flow resistance	0.26
ZGML40X150-21-FL2-A	-75	200		104	Round Ø 22	Yes	Flow resistance	0.34
ZGML40X150-21-FL3	-75	200		104	Oval	No	Flow resistance	0.27
ZGML40X150-21-FL3-A	-75	200		104	Oval	Yes	Flow resistance	0.35
ZGML40X150-21-FS2	-75	200		104	Round Ø 22	No	Flow resistance	0.26
ZGML40X150-21-FS2-A	-75	200		104	Round Ø 22	Yes	Flow resistance	0.34
ZGML40X150-21-FS3	-75	200		104	Oval	No	Flow resistance	0.27
ZGML40X150-21-FS3-A	-75	200		104	Oval	Yes	Flow resistance	0.35
ZGM40X200-21-FL2	-92	171	152		Round Ø 22	No	Flow resistance	0.35
ZGM40X200-21-FL2-A	-92	171	152		Round Ø 22	Yes	Flow resistance	0.43
ZGM40X200-21-FL3	-92	171	152		Oval	No	Flow resistance	0.36
ZGM40X200-21-FL3-A	-92	171	152		Oval	Yes	Flow resistance	0.43
ZGM40X200-21-FS2	-92	171	152		Round Ø 22	No	Flow resistance	0.35
ZGM40X200-21-FS2-A	-92	171	152		Round Ø 22	Yes	Flow resistance	0.43
ZGM40X200-21-FS3	-92	171	152		Oval	No	Flow resistance	0.36
ZGM40X200-21-FS3-A	-92	171	152		Oval	Yes	Flow resistance	0.43
ZGML40X200-21-FL2	-75	200		104	Round Ø 22	No	Flow resistance	0.35
ZGML40X200-21-FL2-A	-75	200		104	Round Ø 22	Yes	Flow resistance	0.43
ZGML40X200-21-FL3	-75	200		104	Oval	No	Flow resistance	0.36
ZGML40X200-21-FL3-A	-75	200		104	Oval	Yes	Flow resistance	0.43
ZGML40X200-21-FS2	-75	200		104	Round Ø 22	No	Flow resistance	0.35
ZGML40X200-21-FS2-A	-75	200		104	Round Ø 22	Yes	Flow resistance	0.43
ZGML40X200-21-FS3	-75	200		104	Oval	No	Flow resistance	0.36
ZGML40X200-21-FS3-A	-75	200		104	Oval	Yes	Flow resistance	0.43
ZGM40X300-31-FL2	-92	341	152		Round Ø 22	No	Flow resistance	0.52
ZGM40X300-31-FL2-A	-92	341	152		Round Ø 22	Yes	Flow resistance	0.6
ZGM40X300-31-FL3	-92	341	152		Oval	No	Flow resistance	0.53
ZGM40X300-31-FL3-A	-92	341	152		Oval	Yes	Flow resistance	0.6
ZGM40X300-31-FS2	-92	341	152		Round Ø 22	No	Flow resistance	0.52
ZGM40X300-31-FS2-A	-92	341	152		Round Ø 22	Yes	Flow resistance	0.6
ZGM40X300-31-FS3	-92	341	152		Oval	No	Flow resistance	0.53
ZGM40X300-31-FS3-A	-92	341	152		Oval	Yes	Flow resistance	0.6
ZGML40X300-31-FL2	-75	362		104	Round Ø 22	No	Flow resistance	0.52
ZGML40X300-31-FL2-A	-75	362		104	Round Ø 22	Yes	Flow resistance	0.6
ZGML40X300-31-FL3	-75	362		104	Oval	No	Flow resistance	0.53
ZGML40X300-31-FL3-A	-75	362		104	Oval	Yes	Flow resistance	0.6
ZGML40X300-31-FS2	-75	362		104	Round Ø 22	No	Flow resistance	0.52
ZGML40X300-31-FS2-A	-75	362		104	Round Ø 22	Yes	Flow resistance	0.6
ZGML40X300-31-FS3	-75	362		104	Oval	No	Flow resistance	0.53
ZGML40X300-31-FS3-A	-75	362		104	Oval	Yes	Flow resistance	0.6
ZGM40X400-31-FL2	-92	341	152		Round Ø 22	No	Flow resistance	0.7
ZGM40X400-31-FL2-A	-92	341	152		Round Ø 22	Yes	Flow resistance	0.77
ZGM40X400-31-FL3	-92	341	152		Oval	No	Flow resistance	0.7
ZGM40X400-31-FL3-A	-92	341	152		Oval	Yes	Flow resistance	0.78

VACUUM GRIPPING SYSTEM

SERIES ZGM

Order no.	► Technical data							
	Max. vacuum level [kPa]	Volume flow [l/min]	Air consumption at 4 bar [l/min]	Air consumption at 6 bar [l/min]	Hole pattern of the sealing element	Air control valve	Valve type of the area gripper	Weight [kg]
ZGM40X400-31-FS2	-92	341	152		Round Ø 22	No	Flow resistance	0.7
ZGM40X400-31-FS2-A	-92	341	152		Round Ø 22	Yes	Flow resistance	0.77
ZGM40X400-31-FS3	-92	341	152		Oval	No	Flow resistance	0.7
ZGM40X400-31-FS3-A	-92	341	152		Oval	Yes	Flow resistance	0.78
ZGML40X400-31-FL2	-75	362		104	Round Ø 22	No	Flow resistance	0.7
ZGML40X400-31-FL2-A	-75	362		104	Round Ø 22	Yes	Flow resistance	0.77
ZGML40X400-31-FL3	-75	362		104	Oval	No	Flow resistance	0.7
ZGML40X400-31-FL3-A	-75	362		104	Oval	Yes	Flow resistance	0.78
ZGML40X400-31-FS2	-75	362		104	Round Ø 22	No	Flow resistance	0.7
ZGML40X400-31-FS2-A	-75	362		104	Round Ø 22	Yes	Flow resistance	0.77
ZGML40X400-31-FS3	-75	362		104	Oval	No	Flow resistance	0.7
ZGML40X400-31-FS3-A	-75	362		104	Oval	Yes	Flow resistance	0.78
ZGM40X500-31-FL2	-92	341	152		Round Ø 22	No	Flow resistance	0.87
ZGM40X500-31-FL2-A	-92	341	152		Round Ø 22	Yes	Flow resistance	0.94
ZGM40X500-31-FL3	-92	341	152		Oval	No	Flow resistance	0.87
ZGM40X500-31-FL3-A	-92	341	152		Oval	Yes	Flow resistance	0.95
ZGM40X500-31-FS2	-92	341	152		Round Ø 22	No	Flow resistance	0.87
ZGM40X500-31-FS2-A	-92	341	152		Round Ø 22	Yes	Flow resistance	0.943
ZGM40X500-31-FS3	-92	341	152		Oval	No	Flow resistance	0.87
ZGM40X500-31-FS3-A	-92	341	152		Oval	Yes	Flow resistance	0.95
ZGML40X500-31-FL2	-75	362		104	Round Ø 22	No	Flow resistance	0.87
ZGML40X500-31-FL2-A	-75	362		104	Round Ø 22	Yes	Flow resistance	0.94
ZGML40X500-31-FL3	-75	362		104	Oval	No	Flow resistance	0.87
ZGML40X500-31-FL3-A	-75	362		104	Oval	Yes	Flow resistance	0.95
ZGML40X500-31-FS2	-75	362		104	Round Ø 22	No	Flow resistance	0.87
ZGML40X500-31-FS2-A	-75	362		104	Round Ø 22	Yes	Flow resistance	0.94
ZGML40X500-31-FS3	-75	362		104	Oval	No	Flow resistance	0.87
ZGML40X500-31-FS3-A	-75	362		104	Oval	Yes	Flow resistance	0.95
ZGM40X600-31-FL2	-92	341	152		Round Ø 22	No	Flow resistance	1
ZGM40X600-31-FL2-A	-92	341	152		Round Ø 22	Yes	Flow resistance	1.1
ZGM40X600-31-FL3	-92	341	152		Oval	No	Flow resistance	1
ZGM40X600-31-FL3-A	-92	341	152		Oval	Yes	Flow resistance	1.1
ZGM40X600-31-FS2	-92	341	152		Round Ø 22	No	Flow resistance	1
ZGM40X600-31-FS2-A	-92	341	152		Round Ø 22	Yes	Flow resistance	1.1
ZGM40X600-31-FS3	-92	341	152		Oval	No	Flow resistance	1
ZGM40X600-31-FS3-A	-92	341	152		Oval	Yes	Flow resistance	1.1
ZGML40X600-31-FL2	-75	362		104	Round Ø 22	No	Flow resistance	1
ZGML40X600-31-FL2-A	-75	362		104	Round Ø 22	Yes	Flow resistance	1.1
ZGML40X600-31-FL3	-75	362		104	Oval	No	Flow resistance	1
ZGML40X600-31-FL3-A	-75	362		104	Oval	Yes	Flow resistance	1.1
ZGML40X600-31-FS2	-75	362		104	Round Ø 22	No	Flow resistance	1
ZGML40X600-31-FS2-A	-75	362		104	Round Ø 22	Yes	Flow resistance	1.1
ZGML40X600-31-FS3	-75	362		104	Oval	No	Flow resistance	1
ZGML40X600-31-FS3-A	-75	362		104	Oval	Yes	Flow resistance	1.1
ZGM50X150-21-FL2	-92	171	152		Round Ø 12	No	Flow resistance	0.36
ZGM50X150-21-FL2-A	-92	171	152		Round Ø 12	Yes	Flow resistance	0.44
ZGM50X150-21-FL3	-92	171	152		Oval	No	Flow resistance	0.35
ZGM50X150-21-FL3-A	-92	171	152		Oval	Yes	Flow resistance	0.43
ZGM50X150-21-FS2	-92	171	152		Round Ø 12	No	Flow resistance	0.36
ZGM50X150-21-FS2-A	-92	171	152		Round Ø 12	Yes	Flow resistance	0.44
ZGM50X150-21-FS3	-92	171	152		Oval	No	Flow resistance	3.5
ZGM50X150-21-FS3-A	-92	171	152		Oval	Yes	Flow resistance	0.43
ZGM50X150-22-FL2	-92	342	304		Round Ø 12	No	Flow resistance	0.39
ZGM50X150-22-FL2-A	-92	342	304		Round Ø 12	Yes	Flow resistance	0.46
ZGM50X150-22-FL3	-92	342	304		Oval	No	Flow resistance	0.38
ZGM50X150-22-FL3-A	-92	342	304		Oval	Yes	Flow resistance	0.45
ZGM50X150-22-FS2	-92	342	304		Round Ø 12	No	Flow resistance	0.39
ZGM50X150-22-FS2-A	-92	342	304		Round Ø 12	Yes	Flow resistance	0.46
ZGM50X150-22-FS3	-92	342	304		Oval	No	Flow resistance	0.38

Order no.	► Technical data							
	Max. vacuum level [kPa]	Volume flow [l/min]	Air consumption at 4 bar [l/min]	Air consumption at 6 bar [l/min]	Hole pattern of the sealing element	Air control valve	Valve type of the area gripper	Weight [kg]
ZGM50X150-22-FS3-A	-92	342	304		Oval	Yes	Flow resistance	0.45
ZGML50X150-21-FL2	-75	200		104	Round Ø 12	No	Flow resistance	0.36
ZGML50X150-21-FL2-A	-75	200		104	Round Ø 12	Yes	Flow resistance	0.44
ZGML50X150-21-FL3	-75	200		104	Oval	No	Flow resistance	0.35
ZGML50X150-21-FL3-A	-75	200		104	Oval	Yes	Flow resistance	0.43
ZGML50X150-21-FS2	-75	200		104	Round Ø 12	No	Flow resistance	0.36
ZGML50X150-21-FS2-A	-75	200		104	Round Ø 12	Yes	Flow resistance	0.44
ZGML50X150-21-FS3	-75	200		104	Oval	No	Flow resistance	0.35
ZGML50X150-21-FS3-A	-75	200		104	Oval	Yes	Flow resistance	0.43
ZGML50X150-22-FL2	-75	400		208	Round Ø 12	No	Flow resistance	0.39
ZGML50X150-22-FL2-A	-75	400		208	Round Ø 12	Yes	Flow resistance	0.46
ZGML50X150-22-FL3	-75	400		208	Oval	No	Flow resistance	0.38
ZGML50X150-22-FL3-A	-75	400		208	Oval	Yes	Flow resistance	0.45
ZGML50X150-22-FS2	-75	400		208	Round Ø 12	No	Flow resistance	0.39
ZGML50X150-22-FS2-A	-75	400		208	Round Ø 12	Yes	Flow resistance	0.46
ZGML50X150-22-FS3	-75	400		208	Oval	No	Flow resistance	0.38
ZGML50X150-22-FS3-A	-75	400		208	Oval	Yes	Flow resistance	0.45
ZGM50X200-21-FL2	-92	171	152		Round Ø 12	No	Flow resistance	0.46
ZGM50X200-21-FL2-A	-92	171	152		Round Ø 12	Yes	Flow resistance	0.54
ZGM50X200-21-FL3	-92	171	152		Oval	No	Flow resistance	0.45
ZGM50X200-21-FL3-A	-92	171	152		Oval	Yes	Flow resistance	0.53
ZGM50X200-21-FS2	-92	171	152		Round Ø 12	No	Flow resistance	0.46
ZGM50X200-21-FS2-A	-92	171	152		Round Ø 12	Yes	Flow resistance	0.54
ZGM50X200-21-FS3	-92	171	152		Oval	No	Flow resistance	0.45
ZGM50X200-21-FS3-A	-92	171	152		Oval	Yes	Flow resistance	0.53
ZGM50X200-22-FL2	-92	342	304		Round Ø 12	No	Flow resistance	0.49
ZGM50X200-22-FL2-A	-92	342	304		Round Ø 12	Yes	Flow resistance	0.56
ZGM50X200-22-FL3	-92	342	304		Oval	No	Flow resistance	0.48
ZGM50X200-22-FL3-A	-92	342	304		Oval	Yes	Flow resistance	0.55
ZGM50X200-22-FS2	-92	342	304		Round Ø 12	No	Flow resistance	0.49
ZGM50X200-22-FS2-A	-92	342	304		Round Ø 12	Yes	Flow resistance	0.56
ZGM50X200-22-FS3	-92	342	304		Oval	No	Flow resistance	0.48
ZGM50X200-22-FS3-A	-92	342	304		Oval	Yes	Flow resistance	0.55
ZGML50X200-21-FL2	-75	200		104	Round Ø 12	No	Flow resistance	0.46
ZGML50X200-21-FL2-A	-75	200		104	Round Ø 12	Yes	Flow resistance	0.54
ZGML50X200-21-FL3	-75	200		104	Oval	No	Flow resistance	0.45
ZGML50X200-21-FL3-A	-75	200		104	Oval	Yes	Flow resistance	0.53
ZGML50X200-21-FS2	-75	200		104	Round Ø 12	No	Flow resistance	0.46
ZGML50X200-21-FS2-A	-75	200		104	Round Ø 12	Yes	Flow resistance	0.54
ZGML50X200-21-FS3	-75	200		104	Oval	No	Flow resistance	0.45
ZGML50X200-21-FS3-A	-75	200		104	Oval	Yes	Flow resistance	0.53
ZGML50X200-22-FL2	-75	400		208	Round Ø 12	No	Flow resistance	0.49
ZGML50X200-22-FL2-A	-75	400		208	Round Ø 12	Yes	Flow resistance	0.56
ZGML50X200-22-FL3	-75	400		208	Oval	No	Flow resistance	0.48
ZGML50X200-22-FL3-A	-75	400		208	Oval	Yes	Flow resistance	0.55
ZGML50X200-22-FS2	-75	400		208	Round Ø 12	No	Flow resistance	0.49
ZGML50X200-22-FS2-A	-75	400		208	Round Ø 12	Yes	Flow resistance	0.56
ZGML50X200-22-FS3	-75	400		208	Oval	No	Flow resistance	0.48
ZGML50X200-22-FS3-A	-75	400		208	Oval	Yes	Flow resistance	0.55
ZGM50X300-31-FL2	-92	341	152		Round Ø 12	No	Flow resistance	0.66
ZGM50X300-31-FL2-A	-92	341	152		Round Ø 12	Yes	Flow resistance	0.73
ZGM50X300-31-FL3	-92	341	152		Oval	No	Flow resistance	0.65
ZGM50X300-31-FL3-A	-92	341	152		Oval	Yes	Flow resistance	0.72
ZGM50X300-31-FS2	-92	341	152		Round Ø 12	No	Flow resistance	0.66
ZGM50X300-31-FS2-A	-92	341	152		Round Ø 12	Yes	Flow resistance	0.73
ZGM50X300-31-FS3	-92	341	152		Oval	No	Flow resistance	0.65
ZGM50X300-31-FS3-A	-92	341	152		Oval	Yes	Flow resistance	0.72
ZGM50X300-32-FL2	-92	682	304		Round Ø 12	No	Flow resistance	0.68
ZGM50X300-32-FL2-A	-92	682	304		Round Ø 12	Yes	Flow resistance	0.76

VACUUM GRIPPING SYSTEM

SERIES ZGM

Order no.	► Technical data							
	Max. vacuum level [kPa]	Volume flow [l/min]	Air consumption at 4 bar [l/min]	Air consumption at 6 bar [l/min]	Hole pattern of the sealing element	Air control valve	Valve type of the area gripper	Weight [kg]
ZGM50X300-32-FL3	-92	682	304		Oval	No	Flow resistance	0.67
ZGM50X300-32-FL3-A	-92	682	304		Oval	Yes	Flow resistance	0.75
ZGM50X300-32-FS2	-92	682	304		Round Ø 12	No	Flow resistance	0.683
ZGM50X300-32-FS2-A	-92	682	304		Round Ø 12	Yes	Flow resistance	0.76
ZGM50X300-32-FS3	-92	682	304		Oval	No	Flow resistance	0.67
ZGM50X300-32-FS3-A	-92	682	304		Oval	Yes	Flow resistance	0.75
ZGML50X300-31-FL2	-75	362		104	Round Ø 12	No	Flow resistance	0.66
ZGML50X300-31-FL2-A	-75	362		104	Round Ø 12	Yes	Flow resistance	0.73
ZGML50X300-31-FL3	-75	362		104	Oval	No	Flow resistance	0.65
ZGML50X300-31-FL3-A	-75	362		104	Oval	Yes	Flow resistance	0.72
ZGML50X300-31-FS2	-75	362		104	Round Ø 12	No	Flow resistance	0.66
ZGML50X300-31-FS2-A	-75	362		104	Round Ø 12	Yes	Flow resistance	0.73
ZGML50X300-31-FS3	-75	362		104	Oval	No	Flow resistance	0.65
ZGML50X300-31-FS3-A	-75	362		104	Oval	Yes	Flow resistance	0.72
ZGML50X300-32-FL2	-75	724		208	Round Ø 12	No	Flow resistance	0.68
ZGML50X300-32-FL2-A	-75	724		208	Round Ø 12	Yes	Flow resistance	0.76
ZGML50X300-32-FL3	-75	724		208	Oval	No	Flow resistance	0.67
ZGML50X300-32-FL3-A	-75	724		208	Oval	Yes	Flow resistance	0.75
ZGML50X300-32-FS2	-75	724		208	Round Ø 12	No	Flow resistance	0.68
ZGML50X300-32-FS2-A	-75	724		208	Round Ø 12	Yes	Flow resistance	0.76
ZGML50X300-32-FS3	-75	724		208	Oval	No	Flow resistance	0.67
ZGML50X300-32-FS3-A	-75	724		208	Oval	Yes	Flow resistance	0.75
ZGM50X400-31-FL2	-92	341	152		Round Ø 12	No	Flow resistance	0.86
ZGM50X400-31-FL2-A	-92	341	152		Round Ø 12	Yes	Flow resistance	0.93
ZGM50X400-31-FL3	-92	341	152		Oval	No	Flow resistance	0.84
ZGM50X400-31-FL3-A	-92	341	152		Oval	Yes	Flow resistance	0.92
ZGM50X400-31-FS2	-92	341	152		Round Ø 12	No	Flow resistance	0.86
ZGM50X400-31-FS2-A	-92	341	152		Round Ø 12	Yes	Flow resistance	0.93
ZGM50X400-31-FS3	-92	341	152		Oval	No	Flow resistance	0.84
ZGM50X400-31-FS3-A	-92	341	152		Oval	Yes	Flow resistance	0.92
ZGM50X400-32-FL2	-92	682	304		Round Ø 12	No	Flow resistance	0.88
ZGM50X400-32-FL2-A	-92	682	304		Round Ø 12	Yes	Flow resistance	0.96
ZGM50X400-32-FL3	-92	682	304		Oval	No	Flow resistance	0.87
ZGM50X400-32-FL3-A	-92	682	304		Oval	Yes	Flow resistance	0.94
ZGM50X400-32-FS2	-92	682	304		Round Ø 12	No	Flow resistance	0.91
ZGM50X400-32-FS2-A	-92	682	304		Round Ø 12	Yes	Flow resistance	0.98
ZGM50X400-32-FS3	-92	682	304		Oval	No	Flow resistance	0.89
ZGM50X400-32-FS3-A	-92	682	304		Oval	Yes	Flow resistance	0.97
ZGML50X400-31-FL2	-75	362		104	Round Ø 12	No	Flow resistance	0.86
ZGML50X400-31-FL2-A	-75	362		104	Round Ø 12	Yes	Flow resistance	0.93
ZGML50X400-31-FL3	-75	362		104	Oval	No	Flow resistance	0.84
ZGML50X400-31-FL3-A	-75	362		104	Oval	Yes	Flow resistance	0.92
ZGML50X400-31-FS2	-75	362		104	Round Ø 12	No	Flow resistance	0.86
ZGML50X400-31-FS2-A	-75	362		104	Round Ø 12	Yes	Flow resistance	0.93
ZGML50X400-31-FS3	-75	362		104	Oval	No	Flow resistance	0.84
ZGML50X400-31-FS3-A	-75	362		104	Oval	Yes	Flow resistance	0.92
ZGML50X400-32-FL2	-75	724		208	Round Ø 12	No	Flow resistance	0.88
ZGML50X400-32-FL2-A	-75	724		208	Round Ø 12	Yes	Flow resistance	0.96
ZGML50X400-32-FL3	-75	724		208	Oval	No	Flow resistance	0.87
ZGML50X400-32-FL3-A	-75	724		208	Oval	Yes	Flow resistance	0.94
ZGML50X400-32-FS2	-75	724		208	Round Ø 12	No	Flow resistance	0.91
ZGML50X400-32-FS2-A	-75	724		208	Round Ø 12	Yes	Flow resistance	0.98
ZGML50X400-32-FS3	-75	724		208	Oval	No	Flow resistance	0.89
ZGML50X400-32-FS3-A	-75	724		208	Oval	Yes	Flow resistance	0.97
ZGM50X500-31-FL2	-92	341	152		Round Ø 12	No	Flow resistance	1.1
ZGM50X500-31-FL2-A	-92	341	152		Round Ø 12	Yes	Flow resistance	1.1
ZGM50X500-31-FL3	-92	341	152		Oval	No	Flow resistance	1
ZGM50X500-31-FL3-A	-92	341	152		Oval	Yes	Flow resistance	1.1
ZGM50X500-31-FS2	-92	341	152		Round Ø 12	No	Flow resistance	1.1

Order no.	► Technical data							
	Max. vacuum level [kPa]	Volume flow [l/min]	Air consumption at 4 bar [l/min]	Air consumption at 6 bar [l/min]	Hole pattern of the sealing element	Air control valve	Valve type of the area gripper	Weight [kg]
ZGM50X500-31-FS2-A	-92	341	152		Round Ø 12	Yes	Flow resistance	1.1
ZGM50X500-31-FS3	-92	341	152		Oval	No	Flow resistance	1
ZGM50X500-31-FS3-A	-92	341	152		Oval	Yes	Flow resistance	1.1
ZGM50X500-32-FL2	-92	682	304		Round Ø 12	No	Flow resistance	1.1
ZGM50X500-32-FL2-A	-92	682	304		Round Ø 12	Yes	Flow resistance	1.2
ZGM50X500-32-FL3	-92	682	304		Oval	No	Flow resistance	1.1
ZGM50X500-32-FL3-A	-92	682	304		Oval	Yes	Flow resistance	1.1
ZGM50X500-32-FS2	-92	682	304		Round Ø 12	No	Flow resistance	1.1
ZGM50X500-32-FS2-A	-92	682	304		Round Ø 12	Yes	Flow resistance	1.2
ZGM50X500-32-FS3	-92	682	304		Oval	No	Flow resistance	1.1
ZGM50X500-32-FS3-A	-92	682	304		Oval	Yes	Flow resistance	1.1
ZGML50X500-31-FL2	-75	362		104	Round Ø 12	No	Flow resistance	1.1
ZGML50X500-31-FL2-A	-75	362		104	Round Ø 12	Yes	Flow resistance	1.1
ZGML50X500-31-FL3	-75	362		104	Oval	No	Flow resistance	1
ZGML50X500-31-FL3-A	-75	362		104	Oval	Yes	Flow resistance	1.1
ZGML50X500-31-FS2	-75	362		104	Round Ø 12	No	Flow resistance	1.1
ZGML50X500-31-FS2-A	-75	362		104	Round Ø 12	Yes	Flow resistance	1.1
ZGML50X500-31-FS3	-75	362		104	Oval	No	Flow resistance	1
ZGML50X500-31-FS3-A	-75	362		104	Oval	Yes	Flow resistance	1.1
ZGML50X500-32-FL2	-75	724		208	Round Ø 12	No	Flow resistance	1.1
ZGML50X500-32-FL2-A	-75	724		208	Round Ø 12	Yes	Flow resistance	1.2
ZGML50X500-32-FL3	-75	724		208	Oval	No	Flow resistance	1.1
ZGML50X500-32-FL3-A	-75	724		208	Oval	Yes	Flow resistance	1.1
ZGML50X500-32-FS2	-75	724		208	Round Ø 12	No	Flow resistance	1.2
ZGML50X500-32-FS2-A	-75	724		208	Round Ø 12	Yes	Flow resistance	1.2
ZGML50X500-32-FS3	-75	724		208	Oval	No	Flow resistance	1.1
ZGML50X500-32-FS3-A	-75	724		208	Oval	Yes	Flow resistance	1.1
ZGM50X600-31-FL2	-92	341	152		Round Ø 12	No	Flow resistance	1.2
ZGM50X600-31-FL2-A	-92	341	152		Round Ø 12	Yes	Flow resistance	1.3
ZGM50X600-31-FL3	-92	341	152		Oval	No	Flow resistance	1.2
ZGM50X600-31-FL3-A	-92	341	152		Oval	Yes	Flow resistance	1.3
ZGM50X600-31-FS2	-92	341	152		Round Ø 12	No	Flow resistance	1.2
ZGM50X600-31-FS2-A	-92	341	152		Round Ø 12	Yes	Flow resistance	1.3
ZGM50X600-31-FS3	-92	341	152		Oval	No	Flow resistance	1.2
ZGM50X600-31-FS3-A	-92	341	152		Oval	Yes	Flow resistance	1.3
ZGM50X600-32-FL2	-92	682	304		Round Ø 12	No	Flow resistance	1.3
ZGM50X600-32-FL2-A	-92	682	304		Round Ø 12	Yes	Flow resistance	1.3
ZGM50X600-32-FL3	-92	682	304		Oval	No	Flow resistance	1.3
ZGM50X600-32-FL3-A	-92	682	304		Oval	Yes	Flow resistance	1.3
ZGM50X600-32-FS2	-92	682	304		Round Ø 12	No	Flow resistance	1.3
ZGM50X600-32-FS2-A	-92	682	304		Round Ø 12	Yes	Flow resistance	1.3
ZGM50X600-32-FS3	-92	682	304		Oval	No	Flow resistance	1.3
ZGM50X600-32-FS3-A	-92	682	304		Oval	Yes	Flow resistance	1.3
ZGML50X600-31-FL2	-75	362		104	Round Ø 12	No	Flow resistance	1.2
ZGML50X600-31-FL2-A	-75	362		104	Round Ø 12	Yes	Flow resistance	1.3
ZGML50X600-31-FL3	-75	362		104	Oval	No	Flow resistance	1.2
ZGML50X600-31-FL3-A	-75	362		104	Oval	Yes	Flow resistance	1.3
ZGML50X600-31-FS2	-75	362		104	Round Ø 12	No	Flow resistance	1.2
ZGML50X600-31-FS2-A	-75	362		104	Round Ø 12	Yes	Flow resistance	1.3
ZGML50X600-31-FS3	-75	362		104	Oval	No	Flow resistance	1.2
ZGML50X600-31-FS3-A	-75	362		104	Oval	Yes	Flow resistance	1.3
ZGML50X600-32-FL2	-75	724		208	Round Ø 12	No	Flow resistance	1.3
ZGML50X600-32-FL2-A	-75	724		208	Round Ø 12	Yes	Flow resistance	1.3
ZGML50X600-32-FL3	-75	724		208	Oval	No	Flow resistance	1.3
ZGML50X600-32-FL3-A	-75	724		208	Oval	Yes	Flow resistance	1.3
ZGML50X600-32-FS2	-75	724		208	Round Ø 12	No	Flow resistance	1.3
ZGML50X600-32-FS2-A	-75	724		208	Round Ø 12	Yes	Flow resistance	1.3
ZGML50X600-32-FS3	-75	724		208	Oval	No	Flow resistance	1.3
ZGML50X600-32-FS3-A	-75	724		208	Oval	Yes	Flow resistance	1.3