


CLAMPING ELEMENTS | MANUAL

HK1200MW

► PRODUCT ADVANTAGES



► small construction

For all common miniature profile rail guides


► Tool-free opening and closing (bi-stable)

By turning the knurled screw

► Maintenance free

Up to 50,000 static clamping cycles

► TECHNICAL DETAILS



① Miniature profile rail guide

- Available for all common miniature profile rail guides

② Stainless knurled screw

- For opening and closing the clamping unit

③ Clamping jaw

- The floating bearings guarantee symmetrical application of force

④ Housing

► INFORMATION ON THE PRODUCTS

APPLICATION SCENARIOS

- Assembly aids
- Optical equipment
- Medical equipment

FURTHER INFORMATION

► Spacer plate

In addition, a spacer plate might have to be ordered as height compensation, depending on the height of the rail carriage (dimension D).


Track manufacturer
NB

Rail type
SEBSW

Rail size
12

Carriage type
B

► TECHNICAL DRAWINGS



► TECHNICAL DATA

| Order No. | HK1200MW |
|---|--|
| Operation | manual |
| Holding force | 150 [N] |
| Theoretical holding force ($\mu=0,1$) | 188 [N] |
| B10d value | 50,000 |
| Positioning accuracy +/- | 0,02 [mm] |
| Operating temperature | -10 ... +70 [°C] |
| Weight | 0,061 [kg] |
| Function | Clamping |
| Condition | N (bistable) remains in current position |
| Installation direction | from above |
| Masking tape can be used | with masking tape |
| Tightening torque | 0,35 [Nm] |

Schematic drawing. General tolerances according to DIN ISO 2768 T1-f/T2-H. Edges according to ISO 13715. Element has no guiding properties. Guidance must be external. The holding force is the maximum force that can be applied in the axial direction. Each clamping and braking element is tested in a 100% inspection before delivery for the specified holding forces on a hardened steel rail with a lightly oiled lubricating layer (ISO-VG 68). The use of other lubricants or rail coatings can influence the coefficient of friction. The operating instructions must be observed before commissioning. We reserve the right to make technical changes in the course of further development. The latest and further data can be found online and in the operating instructions at www.zimmer-group.com.