



# CLAMPING AND BRAKING ELEMENTS | PNEUMATIC MBPS-TELEFON

## ► PRODUCT ADVANTAGES



- **broad range of products**  
For all common profile rail guides
- **Energize to open (NC)**  
through spring-loaded energy storage
- **high durability**  
5 million static clamping cycles
- **Safety element**  
Safe braking in case of energy failure

## ► TECHNICAL DETAILS



- ① **Profile rail guide**
  - Available for all common profile rail guides
- ② **Wedge-type gear**
  - Power transmission between the pistons and clamping jaws and brake shoes
- ③ **Clamping jaws and brake shoes**
  - Pressed at the free surfaces of the profile rail guide
- ④ **Housing**
- ⑤ **Pneumatic piston**
  - The piston moves the wedge-type gear longitudinally
- ⑥ **Spring-loaded energy storage**
  - For non-pressurized closing of the clamping unit

## ► INFORMATION ON THE PRODUCTS

### APPLICATION SCENARIOS


- **Clamping in case of pressure drop**
- **Emergency OFF function**
- **Braking linear motors**

### FURTHER INFORMATION

- **Spacer plate**  
In addition, a spacer plate might have to be ordered as height compensation, depending on the height of the rail carriage (dimension D).
- **Special variants on request, e.g.**
  - With proximity switch monitoring
  - With low opening pressure (3.0 bar)
  - With additional air connection (from above, from the front)

|                    |           |           |               |
|--------------------|-----------|-----------|---------------|
| Track manufacturer | Rail type | Rail size | Carriage type |
| Thomson ✓          | 421 ✓     | 55 ✓      | 413..B ✓      |

## ► TECHNICAL DRAWINGS



## ► TECHNICAL DATA

| Order No.                | MBPS-TELEFON     |
|--------------------------|------------------|
| Operation                |                  |
| Positioning accuracy +/- |                  |
| Operating temperature    | -10 ... +70 [°C] |
| Function                 |                  |
| Condition                |                  |

Schematic drawing. General tolerances according to DIN ISO 2768 T1-4/T2-H. Edges according to ISO 13715. Element has no guiding properties. Guidance must be external. The holding force is the maximum force that can be applied in the axial direction. Each clamping and braking element is tested in a 100% inspection before delivery for the specified holding forces on a hardened steel rail with a lightly oiled lubricating layer (ISO-VG 68). The use of other lubricants or rail coatings can influence the coefficient of friction. The operating instructions must be observed before commissioning. We reserve the right to make technical changes in the course of further development. The latest and further data can be found online and in the operating instructions at [www.zimmer-group.com](http://www.zimmer-group.com).