

# CLAMPING ELEMENTS | ELECTRIC LKE-NICHT-MOEGLICH

## ► PRODUCT ADVANTAGES



- **Energy-efficient (bistable)**  
Opens and closes using 24 V DC voltage
- **Integrated electronics**  
Digital control and status signals
- **Flexible cable outlet**  
For maximum space utilization

## ► TECHNICAL DETAILS



- ① **Profile rail guide**
  - Available for all common profile rail guides
- ② **Eccentric gear**
  - Power transmission between motor and clamping jaw
- ③ **Clamping jaw**
  - Pressed at the free surfaces of the profile rail guide
- ④ **Housing**
- ⑤ **electric drive**
  - For generating clamping force
- ⑥ **Sliding block**
  - For floating bearings
- ⑦ **Emergency actuation**
  - Manual opening possible in case of power supply failure
- ⑧ **Electrical connecting cable**
  - Control and power supply
- ⑨ **Adjusting screw**
  - Correction of the rail tolerance

## ► INFORMATION ON THE PRODUCTS

### APPLICATION SCA- NARIOS

- **Axes with electric positioning**
- **Table traverses in medical applications**
- **Electric clamping of machine tables**

### FURTHER INFORMATION

#### ► **Spacer plate**

In addition, a spacer plate might have to be ordered as height compensation, depending on the height of the rail carriage (dimension D).

Track manufacturer
<b>CPC</b>

Rail type
<b>ARC(ARU)</b>

Rail size
<b>25</b>

Carriage type
<b>ARC-MS</b>

## ► TECHNICAL DRAWINGS



## ► TECHNICAL DATA

Order No.	LKE-NICHT-MOEGLICH
Operation	
Operating temperature	+5 ... +50 [°C]
Function	
Condition	

Schematic drawing. General tolerances according to DIN ISO 2768 T1-f/T2-H. Edges according to ISO 13715. Element has no guiding properties. Guidance must be external. The holding force is the maximum force that can be applied in the axial direction. Each clamping and braking element is tested in a 100% inspection before delivery for the specified holding forces on a hardened steel rail with a lightly oiled lubricating layer (ISO-VG 68). The use of other lubricants or rail coatings can influence the coefficient of friction. The operating instructions must be observed before commissioning. We reserve the right to make technical changes in the course of further development. The latest and further data can be found online and in the operating instructions at [www.zimmer-group.com](http://www.zimmer-group.com).